


Table Edge  
 ~19.95 m from target chamber  
 ~18 degrees



Detector Thickness  
 GEMs 15 mm  
 SC\_A 10 mm  
 SC\_C 20 mm  
 LASPD 20 mm  
 SC\_D 20 mm (Preshower Tile)  
 SC\_B 10 mm

ECal  
 Lead 11 mm  
 Preshower 20 mm  
 Aluminium 20 mm

Detector area  
 SC\_A 50 mm wide 75 mm tall  
 SC\_C 180 mm wide ~45 mm tall  
 SC\_D hexigon 63.5 mm per side  
 LASPD 140 mm wide 400 mm tall

Dept.	Technical reference	Created by <b>Jimmy Caylor</b> 2/21/2023	Approved by
		Document type	Document status
		Title <b>SoLID test stand 18 degree</b>	DWG No.
		Rev.	Date of issue
		Sheet <b>1/1</b>	